

HSE-3 LONG BAR HEAT SEALER



The satisfactory development, manufacture, conversion and application of flexible packaging films necessitates the implementation of precise methods of quality control systems.

The HSE-3 was developed to precisely control the parameters essential in determining the heat seal threshold.

Especially suited for flexible packaging materials, laminates, foils and paper, the HSE-3 features accurate control of temperature, pressure and dwell time of a standard surface area sealing jaw.

With the introduction of a standard test method ASTM F2029-00 and our heat sealer HSE-3, you can be confident that your heat seal threshold measurement is common to all producers, converters and end users of flexible packaging materials and their eventual applications.

Meets ASTM F-2029-00 (only when top/lower jaw heated)

The HSE-3 also features an easy change over jaw arrangement, with quick release nuts holding the jaws in place. Standard flat ground surface jaws are supplied together with a silicone rubber lower jaw single sided sealing. Profiled/Crimped jaws are available with 120° x 1.8mm pitch crimp.



Ground flat sealing bars



Crimped profile sealing jaws matching pair. Normal size 25mm x 300mm but can be anywhere from 5mm up to 25mm wide x 300mm long.



Thermometer and s/s band surface probe to check jaw temperatures.

SPECIFICATION:

Temperature Control:	0 - 300°C (0 - 572°F) 0.1°C resolution +/- 0.5% +/- 1 digit accuracy. Operating temperature accuracy +/- 2°C. Resistance Type 'J' thermocouple sensing. Single independent or dual independent control
Pressure:	0 - 100psi (0 - 6.8 bar, 0 - 689 Kpa) via digital display and transducer. Pressure control through precision regulator. Repeatability +/-0.02 PSI Operation accuracy +/- 5% Supply via factory compressed air line or nitrogen or compressed air bottles min 6 bar (90 psi) max. 7 bar(100 psi). Pressure medium must be clean and dry.
Dwell Time:	0.01 - 99.9 sec. 0.01 sec resolution real time base via quartz crystal +/- 0.01% of range. Operating accuracy +/- 5% (taking into account friction in piston movement).
Delay Time:	0.1 - 99.9 sec. 0.1 sec resolution real time base via quartz crystal , +/- 0.1% of range. Assists with the correct alignment of the pouch/bag/sample.
Footswitch:	Connection port for footswitch operation. Optional footswitch.
Sealing Jaw Std:	Single jaw option: Top heated with silicone rubber (60 shore hardness) 5mm - 25mm wide x 300mm long. Jaws made from aluminium with machine ground flat face. Dual jaw option: Top and Lower heated 5mm -25mm wide x 300mm long. Jaws made from aluminium with machine ground flat face.
Power:	240V AC 50/60 Hz (110V AC voltage available on request)
Option:	Footswitch PVC Dust cover Alarm package for temperature over and under band (selectable). Pressure High/Low alarm. When alarm activated audible alarm sounds and inhibit of sealing initiated. Crimp profiled slide-on jaws 120 deg x 1.8 mm pitch. Cold Seal Option (temperature circuit removed) supplied with flat or crimp profiled jaws. Teflon coated tape or permanent Teflon coating Digital thermometer and s/s band probe to check the actual temperatures of sealing Jaw.